



# Ground Clamp, C-Type, Type I-Class A-Grade 6H, 2.0" Jaw Opening

By CHANCE Utility  
Catalog # [T6000658](#)

Ground Clamp, C-Type, Type I-Class A-Grade 6H, 2.0" Jaw Opening



## Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current - ASTM Grade 6H
- Main Line Range Max. 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 6H, Jaws Smooth
- Drilled ferrule hole for threaded ferrule

## General

Eye Screw/T-Handle Installation Torque (in-lb)	250 in-lb
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359061090

## Dimensions

Jaw Opening Size - Maximum	2 in
Jaw Opening Size - Minimum	.162 in
Weight	2.45 lb

## Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

## Certifications and Compliance

Fault Current - ASTM Grade	6H
----------------------------	----

## Logistics

Carton Quantity	15
Pallet Quantity	450

## Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)  
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301\\_web\)](#)  
[Sales Drawings - SA\\_600-0658](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-T6000658-SPEC-EN | REV 7/2023