



Bus Bar Ground Clamp with Rated Stud, Type I-Class A-Grade 5H, 4.5" Jaw Opening

By CHANCE Utility
Catalog # [T6000819](#)

Bus Bar Ground Clamp with Rated Stud, Type I-Class A-Grade 5H, 4.5" Jaw Opening



Features

- Bus-Bar Ground Clamp
- Continuous Current 400A
- Fault Current 47kA for 15 cycles X/R=30
- Main Line Range Max. 4" x 4" square, 4.5" O.D. Bus
- Main Line Range Min. 4/0 Str CU (0.500")
- Rated 8.5" x 0.75" Stud
- ASTM Type I, Class A, Grade 5H
- Jaws Smooth
- Rated Stud

General

EU RoHS Indicator	No
Eye Screw/T-Handle	300 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Material	Aluminum
UPC	096359061182

Dimensions

Jaw Opening Size - Maximum	4.5 in
Jaw Opening Size - Minimum	.5 in
Weight	5.25 lb

Certifications and Compliance

Fault Current - ASTM Grade	5H
----------------------------	----

Logistics

Carton Quantity	2
Pallet Quantity	48

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301_web\)](#)
[Sales Drawings - SA_G3369](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-T6000819-SPEC-EN | REV 8/2023