



CHANCE® 6ft. #2 Chisel-Point Temporary Grounding Set for URD Cable with Ground Rod

By CHANCE Utility
Catalog # T6002234

CHANCE® 6ft. #2 Chisel-Point Temporary Grounding Set for URD Cable with Ground Rod



*Representative Image

Features

- For temporary grounding of underground distribution cable with jacket over concentric neutral
- Used to confirm the cable that will be worked on is de-energized
- Chisel-point ensures contact with center conductor
- Chisel-point clamp main-line capacity is 1-1/2in.
- C-clamp in chisel-point sets fits conductors from #6 (0.162in.) to 2.0in. O.D. bus
- Each set includes 6ft. of #2 copper clear-jacket ground cable and ferrules, a chisel clamp and C-clamp
- Includes 24in. screw-in copper-clad ground rod for easy handling

General

EU RoHS Indicator No
UPC 096359061700

Dimensions

Jaw Opening Size - Maximum 2 in
Jaw Opening Size - Minimum .162 in
Weight 12.74 lb

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)

[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-T6002234-SPEC-EN | REV 8/2023