



# 15° Cable Spacer / Tangent Standoff Bracket, 21"

By Chance  
Catalog # [T6531191](#)



21" Extra Heavy Duty 15° Fiberglass Cable Spacer / Tangent Standoff Bracket

## Features

- Single position end fitting with clevis
- 2.5" (extra heavy duty) fiberglass rod
- 15° angle
- Base and end fittings are aluminum alloy

## General

Catalog Number	T6531191
Description - End Fitting	Cable Spacer Mount
Strength Rating - Minimum Ultimate, Transverse (T)	10,000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	4,000 lb
UPC	096359062141

## Dimensions

Diameter - Rod / Tube	2.5 in
Dimensions	21 in x 10.5 in x 4 in
Distance From Pole	21 in
Height	4 in
Length	21 in

Mounting Bolt Spacing	8 in
Weight	14.94 lb
Width	10.5 in

## Electrical Ratings

Phase	1-Phase
-------	---------

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

## Logistics

Pallet Quantity	64
Standard Package	2

## Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Sales Drawings - SA6531191](#)
- [Specifications - T6531191](#)



A Hubbell brand