



Anchor, Cross-Plate, 24in painted fits 3/4in rod

By Chance
Catalog # [X2434](#)

Cross-Plate Anchor for 24" (610 mm) Hole used with 0.625" (15.9 mm) or 0.75" (19.1 mm) Diameter Rod.



Features

- Cross-plate anchors are designed to be installed against side of hole. Rod trench is required to align rod with guy load.
- Painted with black paint
- Nut retainer on bottom of anchor holds nut in place during installation
- 1st alternate image: Bottom view of Anchor with Anchor Rod installed. Anchor Rod not included with Anchor
- 2nd alternate image: Top view of Anchor with Anchor Rod installed. Anchor Rod not included with Anchor

General

Application	Earth Tension Anchoring
Catalog Number	X2434
Coating	Black Paint
Type	Earth Tension Anchors
UPC	096359066590

Dimensions

Anchor Hole Size	24 in
Area	400 in ²
Dimensions	23.625 in x 23.625 in x 5.000 in
Height	5 in
Length	23.625 in
Rod Diameter - Order Separately	0.625 in 0.75 in
Weight	34.114 lb
Width	23.625 in

Certifications And Compliance

RUS Listed Reference	z - Anchors, plate
----------------------	--------------------

Logistics

Pallet Quantity	24
Standard Package	1

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06136E_Cross_Plate_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Cross Plate Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification Literature - Anchoring](#)
- [Sales Drawings - Cross-Plate Anchor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-X2434-SPEC-EN | REV 6/2024