



Capstan Hoist 3,000 lb. (Hydraulic)

By Chance Lineman Tools & Equipment
Catalog # [C3081380](#)



CAPSTAN HOIST - 3000LB - HYDRAULIC DRIVE, Improved design features a multiple-planetary drive/backstop-clutch assembled on the center shaft of a steel gear case with full-length internal teeth. This design handles more rugged jobs, extends service life and reduces maintenance. Lightweight yet powerful, these portable hoists move many heavyweight tasks and can get into remote or difficult-access sites. Examples: Setting utility poles, pulling wheeled equipment over obstacles, raising transformers (even over fences in back lots), hoisting heavy insulators, stringing and tensioning conductors, pulling cable (indoors and underground). Operator effort remains low for typical loads simply by adding wraps on the capstan drum. So little effort is required, any crew member can run the hoist. Control is so accurate, loads can be moved fractions of an inch.

Features

- 4 wraps of rope = 1:44 ratio. That is, 1 lb. pull on Fall Line develops 44 lb. on Load Line. Therefore, 20 lb. of pull develops 880 lb. of lift.

General

EU RoHS Indicator	No
Power Supply	Hydraulic
Rope Speed at Rated Load	30' (9 m) per minute
Strength Rating - Ultimate	3000 lb
Style	3,000 lb. Hydraulic Hoist
UPC	096359016052

Dimensions

Dimensions	24 in x 13 in x 12 in
Height	12 in
Length	24 in
Length Metric	61.0 mm
Weight	44.0 lb
WeightMetric	20.0 kg
Width	13 in

Logistics

Standard Package	1
------------------	---

Product Assets

[Literature - Capstan Hoist \(BR09023E\)](#)
[Owner's Manuals - CHANCE® Series 90 Capstan Hoist](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-C3081380-SPEC-EN | REV 1/2024