

Tool, Tension Puller

By Chance Lineman Tools & Equipment
Catalog # [C4000574](#)



*Representative Image

The Hotstick Tension Puller is equipped with rings so that it can be handled and operated with the Grip-All Clampstick or with rubber gloves. Both models feature a hook on each end that is non-swiveling for positive hotstick operation and has a spring-loaded gate which will rotate 135 degrees left or right from closed position. For operational ease the selector lever on the ratchet wrench of these two models has been made larger to accommodate hotsticks.

Features

- Equipped with rings for handling and operation with the Chance Grip-All Clampstick or with rubber gloves
- Non-swiveling hook on each end for positive hotstick operation
- Spring-loaded gate rotates 135° left or right from closed position
- Large, ratchet wrench selector lever easily accommodates hotsticks

General

Style	34.5 kV Puller
UPC	096359016656
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

Dimensions

Dimensions	104.5 in x 13.88 in x 5.06 in
Dimensions Metric	2,654 mm x 35.3 mm x 12.9 mm
Height	5.06 in
Height Metric	12.9 mm
Length	104.5 in
Length Metric	2,654 mm
Weight	17 lb
WeightMetric	7.7 kg
Width	13.88 in
WidthMetric	35.3 mm

Logistics

Pallet Quantity	16
-----------------	----

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)



A Hubbell brand