

Tool, Tension Puller

By Chance Lineman Tools & Equipment
Catalog # [C4000575](#)



*Representative Image

The Hotstick Tension Puller is equipped with rings so that it can be handled and operated with the Grip-All Clampstick or with rubber gloves. Both models feature a hook on each end that is non-swiveling for positive hotstick operation and has a spring-loaded gate which will rotate 135 degrees left or right from closed position. For operational ease the selector lever on the ratchet wrench of these two models has been made larger to accommodate hotsticks.

Features

- Equipped with rings for handling and operation with the Chance Grip-All Clampstick or with rubber gloves
- Non-swiveling hook on each end for positive hotstick operation
- Spring-loaded gate rotates 135° left or right from closed position
- Large, ratchet wrench selector lever easily accommodates hotsticks

General

EU RoHS Indicator	No
Style	69 kV Puller
UPC	096359016663
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

Dimensions

Dimensions	78.0 in x 21.25 in x 3.25 in
Dimensions Metric	1,981 mm x 54.0 mm x 8.3 mm
Height	3.25 in
Height Metric	8.3 mm
Length	78 in
Length Metric	1,981 mm
Weight	22.35 lb
WeightMetric	10.1 kg
Width	21.25 in
WidthMetric	54 mm

Logistics

Pallet Quantity	18
-----------------	----

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)



A Hubbell brand