

Boom Mounted 10' Auxiliary Arm with Adapter for Square Booms

By Chance Lineman Tools & Equipment

Catalog # [C4000744](#)

Three Phase Lift with 2" Diameter x 10' long Auxiliary Arm, Mast, Braces and Adapter to fit to Square Booms

Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Horizontal arm is 2.5" diameter x 10' long
- 4" x 4" mast is fitted with quick mounting assembly Assembly attaches to booms from 5-7/8" x 7-3/8" to 12" x 12", both square and rectangular
- Included 3 C4000268 Small Roller Wireholders (2" wide opening)
- Working end of mast will accept several accessories such as
- Epoxiglas™ Auxiliary Arm
- Single lifting wire holder (C40007470)
- Sheave for gin work (C40007460)
- Auxiliary Arm may be swiveled to and locked into any desired position
- Single lifting wire holder may also be swiveled to maintain conductor alignment
- CHANCE 3 Phase Lifts are intended for vertical lifts in straight line applications
- Electrical Ratings: • GLOSSY, CLEAN AND DRY Epoxiglas™ • 15kV Phase to Phase (20 Inch Min. Wireholder Spacing) • 34kV Phase to Phase (20 Inch Min. Wireholder Spacing) and M48057 Insulators are used on each wireholder



- Mechanical Ratings: Max. Total Load: • Balanced Vertical Load: 1000 lb. • Unbalanced Vertical Load: 800 lb. Rated working load (per wire holder): • Vertical with braces: 200 lb. • Vertical without braces: 150 lb. • Side Load: 100 lb.

General

Catalog Number	C4000744
EU RoHS Indicator	No
Style	Boom Mounted Auxiliary Arm
UPC	096359016762

Dimensions

Weight	159.75 lb
Weight Metric	72.5 kg

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

[Catalogs - Conductor Support Equipment](#)
[Catalogs - Truck Accessories](#)
[Specifications - C4000744](#)