



Two Double Blocks with 120 ft of 1/2 in Samson ULTRA-BLUE 3 Rope

By Chance Lineman Tools & Equipment
Catalog # [C4000914](#)

Rope is pre-installed for immediate use out of the box

Features

- Shells and sheaves are made of high dielectric, fiberfilled natural nylon
- Silicon Bronze Shaft with Oil-Impregnated Bronze Sheave Bearings
- Dielectric rating in dry weather is 30,000 volts between bearing and mounting bolt nut
- Maximum rope diameter accepted is 1/2"

General

EU RoHS Indicator	No
Material	Polyolefin Rope
Max Load Lbs.	3500 lb
Style	2 Double Blocks w/ 120' of Rope
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359016892

Dimensions

Weight	12.5 lb
WeightMetric	5.7 kg

Logistics

Pallet Quantity	24
Standard Package	1

Product Assets

[Catalogs - Load Handling Accessories](#)