

## Double and Triple Blocks with 150 ft of 1/2 in Samson ULTRA-BLUE 3 Rope

By Chance Lineman Tools & Equipment  
Catalog # C4000915



Rope is pre-installed for immediate use out of the box

### Features

- Shells and sheaves are made of high dielectric, fiberfilled natural nylon
- Silicon Bronze Shaft with Oil-Impregnated Bronze Sheave Bearings
- Dielectric rating in dry weather is 30,000 volts between bearing and mounting bolt nut
- Maximum rope diameter accepted is 1/2"

### General

EU RoHS Indicator	No
Material	Polyolefin Rope
Max Load Lbs.	3500 lb
Style	Double & Triple Blocks w/ 150' of Rope
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359016908

### Dimensions

Weight	17 lb
WeightMetric	7.3 kg

### Logistics

Pallet Quantity	24
Standard Package	1

### Product Assets

[Catalogs - Load Handling Accessories](#)