

## Double Block with Becket

By Chance Lineman Tools & Equipment  
Catalog # [C4000919](#)

3,500 lb Max Load Rating with 360 degree Swivel Hook, Spring-loaded Safety Latch, and Hotstick Rings



### Features

- Shells and sheaves are made of high dielectric, fiberfilled natural nylon
- Silicon Bronze Shaft with Oil-Impregnated Bronze Sheave Bearings
- Dielectric rating in dry weather is 30,000 volts between bearing and mounting bolt nut
- Maximum rope diameter accepted is 1/2"

### General

Material	Glass Fiber Filled Nylon
Max Load Lbs.	3500 lb
Style	Double Block w/ Becket
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359016946

### Dimensions

Weight	3.3 lb
WeightMetric	1.5 kg

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Load Handling Accessories](#)  
[Sales Drawings - SAC4000919](#)