

Epoxiglas™ Lever Lift

By Chance Lineman Tools & Equipment
Catalog # [C4001016](#)

Epoxiglas Lever Lift Wire Tong Supports are for the same application as aluminum-base units, but are normally used on higher transmission voltages where more lifting space is required. Epoxiglas unit has a total conductor lift of 36 inches. The arbor adapter (M4760-2) shown above can be used to convert an Epoxiglas lever lift into a double lift for tow wire tongs. The Epoxiglas member is 36" long and provides the same working load per tong as the aluminum units.



Features

- For same applications as aluminum-base units
- Normally used on higher transmission voltages where more lifting space is required
- Has a total conductor lift of 36"
- Arbor adapter (M47602) shown above can be used to convert an Epoxiglas lever lift into a double lift for two wire tongs
- Epoxiglas member is 36" long and provides the same working load per tong as the aluminum units

General

EU RoHS Indicator	No
Strength Rating - Ultimate	1000 lb
Strength Rating - Ultimate Metric	453 kg
Style	Epoxiglas Single Type Lever Lift
Type	Wire Tong
UPC	096359016977

Dimensions

Dimensions	31.25 in x 14.375 in x 8.188 in
Dimensions Metric	79.4 mm x 36.5 mm x 20.8 mm
Height	8.188 in
Height Metric	20.8 mm
Length	31.25 in
Length Metric	79.4 mm
Weight	21.5 lb
WeightMetric	9.8 kg
Width	14.375 in
WidthMetric	36.5 mm

Logistics

Pallet Quantity 12

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4001016-SPEC-EN | REV 6/2024