

## 15 in (381 mm) EPOXIGLAS™ Hoist Link Stick

By Chance Lineman Tools & Equipment  
Catalog # [C4001175](#)



To permit hot-line work with a nylon-strap ratchet hoist, a properly applied link stick insulates the hoist from an energized conductor. The hoist link stick is a 1.25"-diameter EPOXIGLAS™ pole with a steel hook on one end and a butt swivel on the other. To apply the link stick, attach the hook of the stick to a wire grip using the hotstick eye to operate the hook. Complete the application by connecting the nylon-strap hoist to the link stick butt swivel and to a pole or crossarm. Working load limit: 4,000 lb.

### Features

- To permit hot-line work with a nylon-strap ratchet hoist, a properly applied link stick insulates the hoist from an energized conductor
- 1 ¼"-diameter Epoxiglas pole with a steel hook on one end
- Features butt swivel on end opposite of steel hook
- Attach the hook of the stick to a wire grip using the hotstick eye to operate hook
- Complete application by connecting nylon-strap hoist to link stick butt swivel and to pole or crossarm
- Rated working load: 4,000 lb.

### General

EU RoHS Indicator	No
Strength Rating - Ultimate	4000 lb
Style	Link Stick
Swivel Top?	Yes
UPC	096359017011
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

### Dimensions

Dimensions	15 in x 5.25 in x 5.25 in
Dimensions Metric	381 mm x 13.3 mm x 13.3 mm
Height	5.25 in
Height Metric	13.3 mm
Length	15 in
Length Metric	381 mm
Weight	4 lb
WeightMetric	1.8 kg
Width	5.25 in
WidthMetric	13.3 mm

### Logistics

Standard Package 1

### Product Assets

[Catalogs - Load Handling Accessories](#)  
[Installation Manuals - CHANCE® Tools Manuals](#)  
[Sales Drawings - SA400-1175](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
CLTE-C4001175-SPEC-EN | REV 6/2024