

Universal Pole with Plastic Hex Fitting 8 ft (2.4 m)

By Chance Lineman Tools & Equipment
Catalog # [C4001583](#)



POLE, UNIV 8' W/ PLASTIC HEX, Insulating black plastic ferrule accepts the threaded-stud fitting unique to Safety Line brand interchangeable- tool accessories. Made from the same glass-filled nylon materials as universal-tool ferrules, it extends insulation to the end of the tool handle.

*Representative Image

Features

- Tested per OSHA & ASTM F711
- Insulating black plastic ferrule accepts threaded-stud fitting unique to Safety Line brand interchangeable tool accessories
- Made from same glass-filled nylon materials as Chance universal-tool ferrules
- Extends insulation to end of tool handle
- Ferrule may be ordered either separate for retrofit on customer poles or factory-installed on 1-1/4"-diameter Epoxiglas™ poles

General

Catalog Number	C4001583
EU RoHS Indicator	No
Storage Bag Included?	P643-8 (Bag not included. Must be ordered separately.)
Style	Plastic Hex & Plastic Universal Ferrule on Ends
UPC	096359017103

Dimensions

Dimensions	106 in x 2.38 in x 2.38 in
Dimensions Metric	269.2 mm x 6.0 mm x 6.0 mm
Height	2.38 in
Height Metric	6 mm
Length	106 in
Length Metric	269.2 mm
Weight	6 lb
WeightMetric	2.7 kg
Width	2.38 in
WidthMetric	6 mm

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
[Instruction Manual](#)
[Specifications - C4001583](#)