

18 in (457 mm) EPOXIGLAS™ Hoist Link Stick

By Chance Lineman Tools & Equipment
Catalog # [C4002399](#)



To permit hot-line work with a nylon-strap ratchet hoist, a properly applied link stick insulates the hoist from an energized conductor. The hoist link stick is a 1.25"-diameter EPOXIGLAS™ pole with a steel hook on one end and a butt swivel on the other. To apply the link stick, attach the hook of the stick to a wire grip using the hotstick eye to operate the hook. Complete the application by connecting the nylon-strap hoist to the link stick butt swivel and to a pole or crossarm. Working load limit: 4,000 lb.

Features

- To permit hot-line work with a nylon-strap ratchet hoist, a properly applied link stick insulates the hoist from an energized conductor
- 1 ¼"-diameter Epoxiglas pole with a steel hook on one end
- Features butt swivel on end opposite of steel hook
- Attach the hook of the stick to a wire grip using the hotstick eye to operate hook
- Complete application by connecting nylon-strap hoist to link stick butt swivel and to pole or crossarm
- Rated working load: 4,000 lb.

General

EU RoHS Indicator	No
UPC	096359017417
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

Dimensions

Dimensions	18 in x 7.125 in x 6.375 in
Dimensions Metric	457 mm x 18.1 mm x 16.2 mm
Height	6.375 in
Height Metric	16.2 mm
Length	18 in
Length Metric	457 mm
Weight	6 lb
WeightMetric	2.7 kg
Width	7.125 in
WidthMetric	18.1 mm

Product Assets

[Catalogs - Load Handling Accessories](#)
[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand