



# Support Hook for EVH Side Opening Cradle, 15 in (0.3 m)

By Chance Lineman Tools & Equipment  
Catalog # C4010361

HOOK, 15" SUPPORT, One Support Hook Only.



## Features

- For selective removal of any one string in deadend bundles, double, triple or quad
- Eliminates the need for removing top strings in bundle access lower string
- Available in 9', 13' and 16' lengths
- Shipped complete with bridle for attaching to Swivel Boom, an Insulator Retaining Plate and either 15" or 31" Hook Assemblies
- 15" assembly for single or double deadends
- 31" Assembly for removal of bottom strings in 4-bundle deadends, and for double "V"-string assemblies
- 9' Cradle is rated 500 pounds maximum load
- 13' and 16' Cradles are rated at 1000 lbs. maximum load
- Insulator Retaining Plate is dual purpose
- One side of Insulator Retaining Plate is adaptable to 11" insulator bells and the opposite side is adaptable to 12-3/4" insulator bells

## General

EU RoHS Indicator	No
Style	Side-Opening for EHV
UPC	096359017516

## Dimensions

Dimensions	27.56 in x 19.38 in x 8.38 in
Dimensions Metric	70.0 mm x 49.2 mm x 21.3 mm
Height	8.38 in
Height Metric	21.3 mm
Length	27.56 in
Length Metric	70 mm
Weight	14 lb
WeightMetric	6.3 kg
Width	19.38 in
WidthMetric	49.2 mm

## Logistics

Pallet Quantity 20

## Product Assets

[Installation Manuals - CHANCE® Tools Manuals Literature - Transmission Project Tools and Equipment Checklist](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CLTE-C4010361-SPEC-EN | REV 6/2024