

Support Hook for EVH Side Opening Cradle, 31 in (0.7 m)

By Chance Lineman Tools & Equipment

Catalog # [C4010362](#)

HOOK, SUPPORT X 31", One Support Hook Only.

Features

- For selective removal of any one string in deadend bundles, double, triple or quad
- Eliminates the need for removing top strings in bundle access lower string
- Available in 9', 13' and 16' lengths
- Shipped complete with bridle for attaching to Swivel Boom, an Insulator Retaining Plate and either 15" or 31" Hook Assemblies
- 15" assembly for single or double deadends
- 31" Assembly for removal of bottom strings in 4-bundle deadends, and for double "V"-string assemblies
- 9' Cradle is rated 500 pounds maximum load
- 13' and 16' Cradles are rated at 1000 lbs. maximum load
- Insulator Retaining Plate is dual purpose
- One side of Insulator Retaining Plate is adaptable to 11" insulator bells and the opposite side is adaptable to 12-3/4" insulator bells

General

Catalog Number	C4010362
EU RoHS Indicator	No
Style	Side-Opening for EHV
UPC	096359017523

Dimensions

Weight	11.5 lb
WeightMetric	5.2 kg

Logistics

Pallet Quantity	24
-----------------	----

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)
[Specifications - C4010362](#)

