



Heavy Duty Two-Pole Strain Carrier, 18 ft (5.4 m)

By Chance Lineman Tools & Equipment
Catalog # [C4012179](#)



Two-pole Strain Carriers relieve strain from an insulator string to permit removal from energized lines.

*Representative Image

Features

- Nominal Pole Length 18'
- Distance between yokes: minimum 191", maximum 225"

General

Catalog Number C4012179

Dimensions

Maximum Distance Between Yokes 225 in
Maximum Distance Between Yokes Metric 571.5 cm

Minimum Distance Between Yokes	191 in
Minimum Distance Between Yokes Metric	485.1 cm
Weight	105 lb
WeightMetric	47.6 kg

Product Assets

- [Catalogs - Tools and Grounding Catalog Full](#)
- [Catalogs - Transmission Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool Instruction Manual](#)
- [Literature - Transmission Project Tools and Equipment Checklist](#)
- [Sales Drawings - SAC4012174](#)
- [Specifications - C4012179](#)