

## Platform Ladder, 6'

By Chance Lineman Tools & Equipment  
Catalog # [C4020276](#)

Stand or sit at the worksite instead of kneeling on the structure — for convenience and efficiency. Proven products combine in the Platform Ladder: 48"-long Epoxiglas™ Ladder and two 20"-long sections of 10"- wide Platform joined side-by-side constitute a bosun's chair. Adjustable ladder hooks may be added. Platform Ladder may be suspended and tagged-off with rope, wire tongs or a combination of both in order to maneuver a worker into position. For quick rigging and easy storage, Platform Ladder folds into a neat, compact package. Although the Platform Ladder is rated for loads to 500 pounds, users must give serious consideration to the capacity of the point from which it is suspended and the equipment used to suspend it.

### Features

- Allows workers to stand or sit at worksite instead of kneeling on structure
- Convenient and efficient
- Proven products combine in Chance Platform Ladder: 48"-long Epoxiglas™ Ladder and two 20"-long sections of 10"-wide Platform joined side-by-side constitute a bosun's chair
- Adjustable ladder hooks may be added
- Platform Ladder may be suspended and tagged-off with rope, wire tongs or a combination of both in order to maneuver a worker into position
- Platform Ladder folds into a compact package for quick rigging and easy storage
- Although rated for 500-lb. loads, users must give serious consideration to capacity of the point from which it is suspended and the equipment used to suspend it
- For improved footing, three strips of 2" non-skid tape extend the length of the platform

### General

EU RoHS Indicator No  
UPC 096359294511



### Dimensions

Dimensions	108 in x 30 in x 10 in
Dimensions Metric	274.3 mm x 76.2 mm x 25.4 mm
Height	10 in
Height Metric	25.4 mm
Length	108 in
Length Metric	274.3 mm
Weight	124 lb
WeightMetric	56.2 kg
Width	30 in
WidthMetric	76.2 mm

### Product Assets

[Literature - Transmission Project Tools and Equipment Checklist](#)  
[Sales Drawings - SA402-0276](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CLTE-C4020276-SPEC-EN | REV 6/2024