

Insulated Platform, 6 ft

By Chance Lineman Tools & Equipment
Catalog # [C4021043](#)

Unique design features 12 in (.305 m) of insulating 2 in (51 mm) diameter Epoxiglas poles connecting the platform to the mounting bracket. Secures to pole via chain binders from included Fixed Mount.



Features

- Optional Epoxiglas Rail and Pivot Base sold separately
- IMPORTANT: Rail is not suited for use as a fall restraint device
- 6 ft (1.53 m) overall length, platform board is 53.5 in (1.36 m)
- 500 lb. (226.8 kg) Maximum Load Rating
- Insulating members manufactured to same standards as Chance Hotsticks: OSHA subpart V, section 1926.951(d), IEC 60855, and ASTM 711
- Three strips of 2 in (51 mm) wide non-skid tape extend the length of the platform surface

General

Strength Rating - Ultimate	500 lb
Style	Insulated Platform
UPC	096359234708

Dimensions

Dimensions	72 in x 12.13 in x 6.19 in
Dimensions Metric	182.9 mm x 30.8 mm x 15.7 mm
Height	6.19 in
Height Metric	15.7 mm
Length	72 in
Length Metric	182.9 mm
Weight	56 lb
WeightMetric	25.4 kg
Width	12.13 in
WidthMetric	30.8 mm

Logistics

Pallet Quantity	15
-----------------	----

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)
[Video - CHANCE Installation and Safety guide for Platforms](#)



A Hubbell brand