

## Pivot Base for 6 ft or 8 ft Platforms

By Chance Lineman Tools & Equipment  
Catalog # [C4021173](#)

Includes Two 30 in (.76 m) Chain Binders with self-locking handwheels and one hinge pin



### Features

- Handwheel on top and interlocking teeth on two pivot plates provide simple, sure adjustment to work angle needed
- Two sizes vary in height to fit all applicable platforms
- Pivot range permits 140° adjustment in increments of approximately 9° per tooth on matching plates
- Turning Handle raises and lowers upper plate
- Stainless-steel guide pin keeps plates aligned
- Groove in upper plate centers on rib in base to ensure teeth engagement at every angle setting
- Each Pivot Base includes 30" chain binders with self-locking handwheels and one hinge pin

### General

EU RoHS Indicator	No
Style	Pivot Mount
UPC	096359234692

### Dimensions

Length	50 in
Length Metric	127 mm
Weight	32 lb
WeightMetric	14.5 kg
Width	16 in
WidthMetric	40.6 mm

### Logistics

Pallet Quantity	6
-----------------	---

### Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)  
[Installation Manuals - CHANCE® Tools Manuals](#)  
[Sales Drawings - Pivot Attachment 6', 8'](#)



A Hubbell brand