

# All-Angle Cog Wrench, 10 ft

By Chance Lineman Tools & Equipment  
Catalog # [C4030186](#)

Controls on the All-Angle Cog Wrench permit operator efficiency in locating the wrench on energized hardware. The hand-grip steadies the tool and holds the cog housing in place while the pole is rotated, turning the the cogs to engage the wrench on the nut or bolt. The angle of the wrench head in relation to the handle is adjustable within a range of 140 degrees. Wing nuts on either side of the head tighten to hold the head in a friction-locked position during use. This Epoxiglas Hot Line Tool is 112" in diameter with a 38" diameter fiberglass control rod. The hand-grip is aluminum alloy, the cog housing is bronze alloy and the gears are hardened steel.

## Features

- Tested per OSHA & ASTM F711
- 15 ft-lb maximum torque rating
- Controls permit operator efficiency in locating the wrench on energized hardware
- Handgrip steadies tool and holds cog housing in place while pole is rotated, turning cogs to engage wrench on the nut or bolt
- Wrench head angle in relation to handle is adjustable within a range of 140°
- Wing nuts on either side of head tightens to hold head in position during use
- Chance Epoxiglas™ Hot Line Tool is 1-1/2" in diameter with 3/8" diameter fiberglass control rod
- Aluminum alloy handgrip, bronze alloy cog housing, and hardened steel gears

## General

Catalog Number	C4030186
EU RoHS Indicator	No



Storage Bag Included?	P621-10 (Bag not included. Must be ordered separately.)
UPC	096359018001

## Dimensions

Length	120 in
Weight	14.7 lb
WeightMetric	6.6 kg

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

## Product Assets

[Catalogs - Insulated Hand Tools](#)  
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)  
[Instruction Manual](#)  
[Sales Drawings - All Angle Cog Wrench](#)  
[Specifications - C4030186](#)