



Grip-All 4 ft (1.2 m)

By Chance Lineman Tools & Equipment
Catalog # [C4030291](#)

GRIPALL - 4FT 9IN, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.



*Representative Image

Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control “finger” on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or “shotgun”) incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas™ pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

General

Catalog Number	C4030291
EU RoHS Indicator	No
Storage Bag Included?	P643-4 (Bag not included. Must be ordered separately.)

Style	Standard
UPC	096359018032

Dimensions

Dimension - L Length Overall	1.4 m
mm	
Dimension - Length Overall	57 in
inch	
Dimensions	60 in x 5 in x 5 in
Dimensions Metric	152.4 mm x 12.7 mm x 12.7 mm
Height	5 in
Height Metric	12.7 mm
Length	60 in
Length Metric	152.4 mm
Weight	5.7 lb
WeightMetric	2.6 kg
Width	5 in
WidthMetric	12.7 mm

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Insulated Hand Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Sales Drawings - Epoxiglas Gripall](#)
- [Specifications - C4030291](#)

