



Grip-All 10 ft (3.0 m)

By Chance Lineman Tools & Equipment
Catalog # [C4030294](#)



GRIPALL - 10FT 7IN, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry.
CAUTION: Do not clean the plastic head with solvent.

*Representative Image

Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control “finger” on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or “shotgun”) incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas™ pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

General

EU RoHS Indicator	No
Storage Bag Included?	P643-10 (Bag not included. Must be ordered separately.)
Style	Standard
UPC	096359018124

Dimensions

Dimension - L Length Overall mm	3.2 m
Dimension - Length Overall inch	10.58 ft
Dimensions	131 in x 4.38 in x 4.38 in
Dimensions Metric	332.7 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	131 in
Length Metric	332.7 mm
Weight	8 lb
WeightMetric	3.6 kg
Width	4.38 in
WidthMetric	11.1 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)

[Sales Drawings - Epoxiglas Gripall](#)



A Hubbell brand