



## Grip-All Hinged 8 ft (2.4 m) with Universal Head

By Chance Lineman Tools & Equipment  
Catalog # [C4030297A](#)

GRIPALL -HINGED - 8FT 8IN -W/ UNIVERSAL, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.



### General

EU RoHS Indicator	No
Storage Bag Included?	P643-3 (Bag not included. Must be ordered separately.)
Style	Hinged
UPC	096359018186

### Dimensions

Dimensions	102 in x 7.25 in x 7.25 in
Dimensions Metric	259.1 mm x 18.4 mm x 18.4 mm
Height	7.25 in
Height Metric	18.4 mm
Length	102 in
Length Metric	259.1 mm
Weight	11 lb
WeightMetric	5 kg
Width	7.25 in
WidthMetric	18.4 mm

### Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)