

Grip-All Hinged 14 ft (4.2 m)

By Chance Lineman Tools & Equipment
Catalog # [C4030342](#)

GRIPALL - HINGED - 14FT 8IN, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.

Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control "finger" on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or "shotgun") incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas™ pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

General

Catalog Number C4030342



*Representative Image

EU RoHS Indicator	No
Style	Hinged
UPC	096359018278

Dimensions

Dimension - L Length Overall	4.4 m
mm	
Dimension - Length Overall	14.66 ft
inch	
Dimensions	174 in x 7.25 in x 7.25 in
Dimensions Metric	442.0 mm x 18.4 mm x 18.4 mm
Height	7.25 in
Height Metric	18.4 mm
Length	174 in
Length Metric	442 mm
Weight	14 lb
WeightMetric	6.4 kg
Width	7.25 in
WidthMetric	18.4 mm

Certifications And Compliance

Buy American Compliant Contact Manufacturer

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Tools Manuals](#)
[Sales Drawings - SA_C4030296_Hinged_Grip-all](#)
[Specifications - C4030342](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4030342-SPEC-EN | REV 10/2024