



## Grip-All Hinged 14 ft (4.2 m) with Universal Head

By Chance Lineman Tools & Equipment  
Catalog # [C4030342A](#)

The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.



### General

Style	Hinged
UPC	096359696322

### Dimensions

Dimensions	174 in x 9 in x 9 in
Dimensions Metric	442.0 mm x 22.9 mm x 22.9 mm
Height	9 in
Height Metric	22.9 mm
Length	174 in
Length Metric	442 mm
Weight	15 lb
WeightMetric	6.8 kg
Width	9 in
WidthMetric	22.9 mm

### Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)