

## Grip-All Hinged 16 ft (4.8 m)

By Chance Lineman Tools & Equipment  
Catalog # [C4030343](#)

GRIPALL - HINGED - 16FT 8IN, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.

### Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control "finger" on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or "shotgun") incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas™ pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

### General

Catalog Number C4030343  
EU RoHS Indicator No



Style Hinged  
UPC 096359018285

### Dimensions

Dimension - L Length Overall	5.1 m
mm	
Dimension - Length Overall	200 in
inch	
Dimensions	198 in x 7.25 in x 7.25 in
Dimensions Metric	502.9 mm x 18.4 mm x 18.4 mm
Height	7.25 in
Height Metric	18.4 mm
Length	198 in
Length Metric	502.9 mm
Weight	20 lb
WeightMetric	9.1 kg
Width	7.25 in
WidthMetric	18.4 mm

### Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

### Product Assets

[Catalogs - Insulated Hand Tools](#)  
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)  
[Instruction Manual](#)  
[Sales Drawings - SA\\_C4030296\\_Hinged\\_Grip-all](#)  
[Specifications - C4030343](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
CLTE-C4030343-SPEC-EN | REV 3/2025