

# Insulated Hydraulically Operated Conductor Cutter For Up To 954 MCM ACSR, 6 ft

By Chance Lineman Tools & Equipment  
Catalog # [C4030731](#)

For cutting conductors up to 954 MCM ACSR, All-Aluminum and  
500 MCM copper.

## Features

- Operates like an hydraulic jack- a knob-handle is turned to enable the lineman to operate the pump handle
- Knob is turned in the opposite direction to allow the cutting head to open
- Epoxiglas pole, handle, and hydraulic hose are tested to 100 kV per foot
- Hydraulic oil has a dielectric strength of 25 + kV per ASTM D877-64
- Hose minimum burst strength is 12,000 PSI
- Pump provides maximum pressure of 9,000 PSI
- Cuts without flattening conductor
- Jaws are adjustable to compensate for wear
- Hydraulic hose is located outside the pole for easy maintenance

## General



Catalog Number	C4030731
EU RoHS Indicator	No
Storage Bag Included?	T306-0007 (Bag not included. Must be ordered separately.)
Style	Scissors Jaw
UPC	096359018469

## Dimensions

Length	72 in
Weight	18.1 lb
WeightMetric	8.2 kg

## Product Assets

[Sales Drawings - Hydraulic Wire Cutter](#)  
[Specifications - C4030731](#)