



Insulated Hydraulic Conductor Cutter For Up To 954 MCM ACSR, 8 ft

By Chance Lineman Tools & Equipment
Catalog # [C4030732](#)

HYDRAULIC WIRE CUTTER - 8FT - cuts conductors up to 954 MCM ACSR, All-Aluminum and 500 MCM copper.

Features

- Operation is similar to that of an hydraulic jack
- The Epoxiglas pole, handle and hydraulic hose are tested to 100 kV per foot
- Hydraulic oil has a dielectric strength of 25 + kV per ASTM D877-64
- Hose minimum burst strength is 12,000 PSI
- Pump maximum pressure is 9,000 PSI
- Adjustable jaws designed to cut without flattening the conductor
- Hydraulic hose is located outside the pole for easy maintenance

General

Catalog Number	C4030732
EU RoHS Indicator	No



Storage Bag Included?	T306-0008 (Bag not included. Must be ordered separately.)
Style	Scissors Jaw
UPC	096359018476

Dimensions

Length	96 in
Weight	19.8 lb
WeightMetric	8.9 kg

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

[Catalogs - Cutters](#)
[Specifications - C4030732](#)



A Hubbell brand