

**Hot Rodder Tool, 11/16 in (17 mm)  
Wire dia, 3.0 in (76 mm) Loop**

By Chance Lineman Tools & Equipment  
Catalog # [C4030834](#)

TOOL, ARMOR ROD APPLICATION, Ideal for applying line ties and other formed wire products on energized lines. The loop type work end permits rotational control which is difficult with conventional tying tools.

**Features**

- Designed to fit Universal Poles and any CHANCE Insulated Hand Tool with a universal fitting
- Ideal for applying line ties and other formed wire products on energized lines
- The loop type work end permits rotational control

**General**

Catalog Number	C4030834
EU RoHS Indicator	No
Style	Hot Rodder Tool
UPC	096359018568

**Dimensions**

Dimension - D inch	1 3/4 in
Dimension - G inch	11/16 in
Dimensions	16.25 in x 16.25 in x 5 in
Dimensions Metric	41.3 mm x 41.3 mm x 12.7 mm



\*Representative Image

Height	5 in
Height Metric	12.7 mm
Length	16.25 in
Length Metric	41.3 mm
Weight	13 oz
WeightMetric	0.3 kg
Width	16.25 in
WidthMetric	41.3 mm

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Carton Quantity	50
-----------------	----

**Product Assets**

[Catalogs - Insulated Hand Tools](#)  
[Specifications - C4030834](#)