



Grip-All Telescoping 5 ft 7 in to 8 ft (1.7 to 2.4 m)

By Chance Lineman Tools & Equipment
Catalog # [C4031035](#)

GRIPALL -TELESCOPING - 5FT 6.75IN - 8FT, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.



*Representative Image

Features

- Tested per OSHA & ASTM F711
- Available in two sizes, each readily locks at variable working lengths
- Design features rotating coupler and an engineered positive-lock button with safety stop to keep sections from parting or hook releasing while in use
- Mechanism locks sections into a solid, rattle-free tool
- Black head makes it obvious head is not included in minimum approach distance
- Can replace several conventional clampsticks
- Allows linemen to adhere to safe-working distances and positioning needs, with fewer sticks
- Reduces the number of clampsticks required on a line truck, saving limited storage space
- Engineered interface between sections ensure tool retracts with full control
- Close fit helps keep out dirt and moisture
- Top section is made with foam-center Epoxiglas™ insulated pole
- Functions of this telescoping style are identical to fixed-length style
- All controls can be easily accessed while wearing gloves
- Easy to disassemble, stick must be kept clean and dry inside to ensure long life
- T4031245 Button and Spring Replacement Kit

General

EU RoHS Indicator	No
Storage Bag Included?	P643-6 (Bag not included. Must be ordered separately.)
Style	Telescoping
UPC	096359018841

Dimensions

Dimensions	96 in x 4.38 in x 4.38 in
Dimensions Metric	243.8 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	96 in
Length - Retracted	5.22 ft
Length - Retracted Metric	1.5 m
Length Metric	243.8 mm
Weight	10 lb
WeightMetric	4.5 kg
Width	4.38 in
WidthMetric	11.1 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)

[Sales Drawings - Telescoping Gripall](#)



A Hubbell brand