



Insulated Conductor Cutter For 600 MCM A.A. / 350 MCM Cu, 21-1/2"

By Chance Lineman Tools & Equipment
Catalog # [C4031421](#)

Three standard models offer choice of insulated long or short handles on cutters for soft wire and insulated long handles on cutters for ACSR. orange 112" dia. Epoxiglas® handles have black rubber cushion grips. Shear-type blades cut without deforming cable. These heat-treated tool-steel cutter heads are the same as those for Ratchet Cable Cutters and may be interchanged in the field. Order replacement or spare cutter heads as separate items.



*Representative Image

Features

- Three standard models
- Choice of insulated long or short handles on cutters for soft wire, and insulated long handles on cutters for ACSR
- Chance orange 1½" diameter Epoxiglas® handles have black rubber cushion grips
- Shear-type blades cut without deforming cable
- Heat-treated tool-steel cutter heads are same as Chance Ratchet Cable Cutters
- Note: ACSR head is not for use with 15½" handles
- Soft-wire head must not be used to cut ACSR as it will damage the cutting edges
- Storage bags to fit short or long cutters should be ordered as separate items
- Storage bags are heavy-duty yellow vinyl-impregnated nylon cloth
- Cutters are designed for energized applications
- Users must wear rubber gloves and observe all applicable working clearances when cutting energized conductors

General

EU RoHS Indicator	No
Storage Bag Included?	C306-0023 (Bag not included. Must be ordered separately.)
Type	Cutters
UPC	096359019114

Dimensions

Length	25 in
Weight	4.4 lb
WeightMetric	1.9 kg

Conductor Related

Conductor Size 600 MCM A.A. / 350 MCM Cu.

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)

