



Insulated Conductor Cutter For 336.4 MCM ACSR, 33-1/2"

By Chance Lineman Tools & Equipment
Catalog # [C4031423](#)

Three standard models offer choice of insulated long or short handles on cutters for soft wire and insulated long handles on cutters for ACSR. orange 1 1/2" dia. Epoxiglas® handles have black rubber cushion grips. Shear-type blades cut without deforming cable. These heat-treated tool-steel cutter heads are the same as those for Ratchet Cable Cutters and may be interchanged in the field. Order replacement or spare cutter heads as separate items.



Features

- Three standard models
- Choice of insulated long or short handles on cutters for soft wire, and insulated long handles on cutters for ACSR
- Chance orange 1 1/2" diameter Epoxiglas® handles have black rubber cushion grips
- Shear-type blades cut without deforming cable
- Heat-treated tool-steel cutter heads are same as Chance Ratchet Cable Cutters
- Note: ACSR head is not for use with 15 1/2" handles
- Soft-wire head must not be used to cut ACSR as it will damage the cutting edges
- Storage bags to fit short or long cutters should be ordered as separate items
- Storage bags are heavy-duty yellow vinyl-impregnated nylon cloth
- Cutters are designed for energized applications
- Users must wear rubber gloves and observe all applicable working clearances when cutting energized conductors

General

Storage Bag Included?	C306-0000 (Bag not included. Must be ordered separately.)
Type	Cutters
UPC	096359019138

Dimensions

Length	16.125 in
Weight	4.9 lb
WeightMetric	2.2 kg

Conductor Related

Conductor Size	336.4 MCM ACSR
----------------	----------------

Logistics

Pallet Quantity	32
-----------------	----

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4031423-SPEC-EN | REV 6/2024