



# 15kV Load-Pickup Tool Set 12 ft (3.6 m) #2 Orange Jumper Handle

By Chance Lineman Tools & Equipment  
Catalog # [C4031558](#)



12 ft LOAD-PICK TOOL SET #2 15kV, ORANGE JUMPER HANDLE

## Features

- Rated to pickup and carry up to 200 amp loads at 15kV
- Includes Load-Pickup Device, Orange Jumper Clamp, and 12ft of #2 15kV Jumper Cable
- Load-Pickup Tool and Jumper Clamp fit conductors from #6 Copper (0.162") through 795 ACSR (1.108")
- Clean and inspect Load-Pickup Tool head after every 25 operations or at least once every 90 days
- Adequate rubber gloves must be worn when using this equipment
- Orange-tinted translucent Lexan® housing permits easy visual inspection of the Load-Pickup head

## General

Cable Length	12 ft
Cable Length Metric	3.6 m
EU RoHS Indicator	No
Style	Complete Set
UPC	096359019152

## Dimensions

Length	12 ft
Weight	18.6 lb
WeightMetric	8.4 kg

## Electrical Ratings

Amperage Rating	200
Current Rating	200 A
Voltage - Maximum	15 kV

## Conductor Related

Conductor Diameter (Main) - Maximum	1.108 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	#2 AWG

## Product Assets

[Sales Drawings - SA\\_C4031631\\_LOAD\\_PICK\\_UP\\_TOOL](#)  
[Video - Chance Load Pick-Up Maintenance](#)



A Hubbell brand