

15kV Load-Pickup Tool Set 12 ft (3.6 m) 1/0 Orange Jumper Handle

By Chance Lineman Tools & Equipment
Catalog # [C4031560](#)



12 ft LOAD-PICK TOOL SET 1/0 15kV, ORANGE JUMPER HANDLE

Features

- Rated to pickup and carry up to 250 amp loads at 15kV
- Includes Load-Pickup Device, Orange Jumper Clamp, and 12ft of 1/0 15kV Jumper Cable
- Load-Pickup Tool and Jumper Clamp fit conductors from #6 Copper (0.162") through 795 ACSR (1.108")
- Clean and inspect Load-Pickup Tool head after every 25 operations or at least once every 90 days
- Adequate rubber gloves must be worn when using this equipment
- Orange-tinted translucent Lexan® housing permits easy visual inspection of the Load-Pickup head

General

Cable Length	12 ft
Cable Length Metric	3.6 m
Style	Complete Set
UPC	096359019176

Dimensions

Length	12 ft
Weight	23 lb
WeightMetric	10.4 kg

Electrical Ratings

Amperage Rating	250
Current Rating	250 A
Voltage - Maximum	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	1.108 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	1/0 AWG

Logistics

Pallet Quantity 32

Product Assets

[Sales Drawings - SA_C4031631_LOAD_PICK_UP_TOOL](#)
[Video - Chance Load Pick-Up Maintenance](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4031560-SPEC-EN | REV 6/2024