



# Disconnect Stick, 1-1/4"X4' W/ Plastic Universal Head

By Chance Lineman Tools & Equipment  
Catalog # [C4032046](#)

SECTIONAL UNIVERSAL STICK 1.25IN X 4FT, Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.



\*Representative Image

## Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

## General

EU RoHS Indicator	No
Storage Bag Included?	P620-4 (Bag not included. Must be ordered separately.)
Style	Plastic Universal Head & Male Splice
UPC	096359019626

## Dimensions

Dimensions	54.0 in x 2.38 in x 2.38 in
Height	2.38 in
Length	54.0 in
Length Metric	137.2 mm
Weight	2.0 lb
WeightMetric	0.9 kg
Width	2.38 in

## Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)  
[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-C4032046-SPEC-EN | REV 1/2024