

Sectional Disconnect Stick 1.5 in (38 mm) X 8 ft (2.4 m) with Standard Disconnect Head

By Chance Lineman Tools & Equipment
Catalog # [C4032057](#)

SECTIONAL DISCONNECT STICK 1.5IN X 8FT, Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.

Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

General

EU RoHS Indicator	No
Storage Bag Included?	P620-8 (Bag not included. Must be ordered separately.)
Style	Standard Disconnect Head & Male Splice
UPC	096359019732



*Representative Image

Dimensions

Dimensions	106.0 in x 4.38 in x 4.38 in
Dimensions Metric	269.2 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	106 in
Length Metric	269.2 mm
Weight	3.5 lb
WeightMetric	1.6 kg
Width	4.38 in
WidthMetric	11.1 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4032057-SPEC-EN | REV 6/2024