

Sectional Disconnect Stick 1.5 in (38 mm) X 10 ft (3.0 m) with Standard Disconnect Head

By Chance Lineman Tools & Equipment
Catalog # [C4032058](#)

SECTIONAL DISCONNECT STICK 1.5IN X 10FT, Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.

Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

General

Catalog Number	C4032058
EU RoHS Indicator	No
Storage Bag Included?	P620-10 (Bag not included. Must be ordered separately.)
Style	Standard Disconnect Head & Male Splice
UPC	096359019749



*Representative Image

Dimensions

Dimensions	130.0 in x 4.38 in x 4.38 in
Dimensions Metric	330.2 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	130 in
Length Metric	330.2 mm
Weight	12 lb
WeightMetric	5.4 kg
Width	4.38 in
WidthMetric	11.1 mm

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
[Instruction Manual](#)
[Specifications - C4032058](#)