



# Disconnect Stick, 1-1/4"X4', Non-Metallic Head

By Chance Lineman Tools & Equipment  
Catalog # C4032059

Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.



\*Representative Image

## Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

## General

Storage Bag Included?	P620-4 (Bag not included. Must be ordered separately.)
Style	Non-Metallic Disconnect Head & Male Splice
UPC	096359019756

## Dimensions

Dimensions	54 in x 4.38 in x 4.38 in
Height	4.38 in
Length	54 in
Length Metric	137.2 mm
Weight	5 lb
WeightMetric	2.3 kg
Width	4.38 in

## Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)  
[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>  
[Sales Drawings - SA\\_403-2053](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-C4032059-SPEC-EN | REV 1/2024