



Disconnect Extension Section, 1-1/4"X6'

By Chance Lineman Tools & Equipment
Catalog # C4032063

SECTIONAL STICK EXTENSION 1.25IN X 6FT Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.



*Representative Image

Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

General

EU RoHS Indicator	No
Storage Bag Included?	P620-6 (Bag not included. Must be ordered separately.)
Style	Extension Section; Male & Female Ends
UPC	096359019787

Dimensions

Dimensions	79.0 in x 2.38 in x 2.38 in
Height	2.38 in
Length	79.0 in
Length Metric	200.7 mm
Weight	2.3 lb
Weight Metric	1.0 kg
Width	2.38 in

Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)
[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)<LineBreak/>



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-C4032063-SPEC-EN | REV 1/2024