



# Disconnect Extension Section 1.5 in (38 mm) X 6 ft (1.8 m)

By Chance Lineman Tools & Equipment  
Catalog # C4032066



SECTIONAL STICK EXTENSION 1.5IN X 6FT, Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.

## Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

## General

Catalog Number	C4032066
EU RoHS Indicator	No
Storage Bag Included?	P620-6 (Bag not included. Must be ordered separately.)
Style	Extension Section; Male & Female Ends
UPC	096359019817

## Dimensions

Dimensions	74.0 in x 2.38 in x 2.38 in
Dimensions Metric	188.0 mm x 6.0 mm x 6.0 mm
Height	2.38 in
Height Metric	6 mm
Length	74 in
Length Metric	188 mm
Weight	2.5 lb
WeightMetric	1.1 kg
Width	2.38 in
WidthMetric	6 mm

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

## Product Assets

- [Catalogs - Insulated Hand Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Specifications - C4032066](#)