

## Base Cap 1.5 in X 5 in (38 X 127 mm)

By Chance Lineman Tools & Equipment  
Catalog # [C4032070](#)



SECTIONAL STICK BASE CAP 1.5IN X 5IN, Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.

### Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

### General

EU RoHS Indicator	No
Style	Base Cap; Female Splice
UPC	096359019855

### Dimensions

Dimensions	10.0 in x 2.38 in x 2.38 in
Dimensions Metric	25.4 mm x 6.0 mm x 6.0 mm
Height	2.38 in
Height Metric	6 mm
Length	10 in
Length Metric	25.4 mm
Weight	1 lb
WeightMetric	0.5 kg
Width	2.38 in
WidthMetric	6 mm

### Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand