



Disconnect Stick 1.25 in (32 mm) X 6 in (15 cm)

By Chance Lineman Tools & Equipment
Catalog # C4032073

SECTIONAL DISCONNECT STICK 1.25IN X 6IN, Non-conductive splices snap together for just the right job length. Compact fittings interchange on orange Epoxiglas™ insulated sections, store in limited space. For quick assembly and long life, metal buttons are rounded and springs of stainless steel. Silicone coating and gloss finish seal out moisture. Base cap included with top sections.

Features

- Tested per OSHA & ASTM F711
- Non-conductive splices snap together for just the right job length
- Compact fittings interchange on orange Epoxiglas™ insulated sections
- Easily store in limited space
- Rounded metal buttons and stainless-steel springs for long life
- Silicone coating and gloss finish seal out moisture
- Base cap included with top sections
- Extension Sections (Both Sizes: 4', 6', 8' and 10' lengths, with female fitting at top and male fitting at bottom)

General

Catalog Number	C4032073
EU RoHS Indicator	No
Style	Standard Switch Disconnect Head & Male Splice



*Representative Image

UPC 096359019886

Dimensions

Dimensions	15.0 in x 6 in x 6 in
Dimensions Metric	38.1 mm x 15.2 mm x 15.2 mm
Height	6 in
Height Metric	15.2 mm
Length	15 in
Length Metric	38.1 mm
Weight	1 lb
WeightMetric	0.5 kg
Width	6 in
WidthMetric	15.2 mm

Product Assets

- [Installation Manuals - CHANCE® Tools Manuals](#)
- [Sales Drawings - SA_403-2053](#)
- [Specifications - C4032073](#)