

Heavy Duty Flexible Insulated Wrench, 8 ft 3 in (2.5 m) with 1/2 in Flexible and Fixed Square Drives

By Chance Lineman Tools & Equipment
Catalog # [C4032137](#)

Used for tightening nuts on hardware fittings on high-voltage lines



*Representative Image

Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Made using heavy duty 1.5" Diameter Epoxiglas Pole
- Overall Length is 6'3"
- 75 ft-lb torque rating
- Standard square socket in lower end accepts 1/2" square-shank ratchet or similar hand tools
- Square shank on upper end fits any 1/2"-drive socket
- Universal joint coil spring limits flexibility, giving operator socket control at various angles
- Spring is easily removed for lubrication

General

Catalog Number	C4032137
EU RoHS Indicator	No
Storage Bag Included?	P643-6 (Bag not included. Must be ordered separately.)
Style	w/ Flexible 1/2" Sq. Plug & Fixed 1/2" Sq. Socket
Torque Rating	75 ft-lbs
UPC	096359019954

Dimensions

Dimensions	79.0 in x 3.38 in x 3.38 in
Dimensions Metric	2006.6 mm x 8.6 mm x 8.6 mm
Height	3.38 in
Height Metric	8.6 mm
Length	79 in
Length Metric	2006.6 mm
Weight	5.5 lb
Weight Metric	2.5 kg
Width	3.38 in
Width Metric	8.6 mm

Certifications And Compliance

Buy American Compliant Contact Manufacturer

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Sales Drawings - SA_403-2136](#)
[Specifications - C4032137](#)