



Heavy-Duty Adjustable Stick W/ Universal Fitting, 10' - 14'

By Chance Lineman Tools & Equipment
Catalog # C4032604

HD ADJ STICK W/UNIV FITTING, 10'-14', Clearly marked at each 1-foot extension lock, one of these tools can replace as many as eight single-length hotsticks. Especially for such tight confines as substations, these adjustable sticks can be stored in standard-length cannisters and avoid the difficulties of working extra-long sticks through busswork structures. Classified as Heavy-Duty due to its large (1.25"-diameter) insulated top section and 1.5"-O.D. epoxy-reinforced fiberglass base tube.



*Representative Image

Features

- Tested per OSHA & ASTM F711
- For substations and close-clearance worksites
- Clearly marked at each 1' extension lock
- One of these tools can replace as many as eight singlelength hotsticks
- Adjustable sticks can be stored in short collapsed lengths and to avoid difficulties of maneuvering extra-long sticks through busswork structures
- Heavy-duty construction - Classified as Heavy-Duty due to its large (1-1/4"-diameter) insulated top section and 1-1/2"-O.D. epoxy-reinforced fiberglass base tube
- 24" overlap at usable-length extremes - In each size, a 2' section of Epoxiglas™ foam-core top section remains inside the base section at the longest locked, usable length and At the shortest locked length, insulated top section extends a full 2' beyond base

General

EU RoHS Indicator	No
Storage Bag Included?	P621-8 (Bag not included. Must be ordered separately.)
Style	Universal Head
UPC	096359020158

Dimensions

Dimensions	168 in x 2.38 in x 2.38 in
Height	2.38 in
Length	168 in
Length - Retracted	98.4 in
Length Metric	426.7 mm
Lengths - Extended	<ul style="list-style-type: none"> • 10 • 11 • 12 • 13 • 14
Weight	10.0 lb
WeightMetric	4.5 kg
Width	2.38 in

Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)
[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)
[Sales Drawings - Adjustable Substation Stick](#)



A proud member of the Hubbell Family.