



Grip-All Telescoping 8 ft 10 in to 14 ft 3 in (2.6 to 4.3 m) with Universal Head

By Chance Lineman Tools & Equipment
Catalog # [C4033061](#)

GRIPALL-TELESCOPING 8FT10.5IN-14FT3.75IN, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.



Features

- Tested per OSHA & ASTM F711
- Available in two sizes, each readily locks at variable working lengths
- Design features rotating coupler and an engineered positive-lock button with safety stop to keep sections from parting or hook releasing while in use
- Mechanism locks sections into a solid, rattle-free tool
- Black head makes it obvious head is not included in minimum approach distance
- Can replace several conventional clampsticks
- Allows linemen to adhere to safe-working distances and positioning needs, with fewer sticks
- Reduces the number of clampsticks required on a line truck, saving limited storage space
- Engineered interface between sections ensure tool retracts with full control
- Close fit helps keep out dirt and moisture
- Top section is made with foam-center Epoxiglas™ insulated pole
- Functions of this telescoping style are identical to fixed-length style
- All controls can be easily accessed while wearing gloves
- Easy to disassemble, stick must be kept clean and dry inside to ensure long life
- T4031245 Button and Spring Replacement Kit

General

EU RoHS Indicator	No
Storage Bag Included?	P643-8 (Bag not included. Must be ordered separately.)
Style	Telescoping Style with Universal Fitting on Handle
UPC	096359020349

Dimensions

Dimensions	168 in x 6.0 in x 5 in
Dimensions Metric	426.7 mm x 15.2 mm x 12.7 mm
Height	5 in
Height Metric	12.7 mm
Length	168 in
Length - Retracted	8.54 ft
Length - Retracted Metric	2.6 m
Length Metric	426.7 mm
Weight	14 lb
WeightMetric	6.4 kg
Width	6 in
WidthMetric	15.2 mm

Product Assets

[Customer Notices - Prop 65 Notice](#)

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand