

Digital Phasing Meter to 40kV

By Chance Lineman Tools & Equipment
Catalog # [C4033370](#)

Large, backlit, direct-reading display easily determines phase relationships and approximate voltage, line-to-line or line-to-ground



*Representative Image

Features

- Large Digital Display with Backlight, Hold, and Sleep modes
- Two high-impedance components in fiberglass poles, each threaded for interchangeable probes
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- 40kV Unit not suitable for Hi-Pot Testing
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks (Not Included) of appropriate length

General

EU RoHS Indicator	No
Style	Digital Display
UPC	096359368113

Dimensions

Weight	14.5 lb
WeightMetric	6.5 kg

Electrical Ratings

Withstand Voltage	40kV
-------------------	------

Logistics

Standard Package	1
------------------	---

Product Assets

[Installation Manuals - CHANCE Digital Phasing Testers Operating Instructions](#)

[Video - CHANCE Meters and Instruments](#)