

Auto-Ranging Voltage Indicator (ARVI) for Transmission 69kV to 500kV

By Chance Lineman Tools & Equipment
Catalog # [C4033375](#)

For Transmission voltage ranges.

Features

- Makes hot-line voltage testing easier than ever
- State-of-the-art electronics eliminate need for selector switch
- Automatic-ranging function quickly displays approximate phase-to-phase voltage class
- Provides easy, yet reliable means for operator to determine if a line is: De-energized, or Carrying less than normal system voltage from any source or induced voltage from an adjacent live circuit, or Energized at full system voltage
- Simple-to-operate tester attaches to an Epoxiglas™ insulating universal handle of appropriate length to maintain proper OSHA working clearances
- Single push button activates the instrument, then a single light indicates either Power On (by glowing solid) or Low Battery (by blinking)
- With good battery condition, instrument performs a confirming self-test
- It does this by illuminating each of the six indicator lights in series while emitting an alternating audible signal
- Then the probe can be brought into contact with the conductor
- It automatically begins detecting at approximately 69 kV and holds display of one of voltage classes: 69 kV, 115 kV, 161 kV, 230 kV, 345 kV or 500 kV phase-to phase
- Audible signal begins as a slow beeping, becoming faster as final reading is displayed
- When not in use, unit's energy-saving Sleep mode automatically conserves battery



General

Catalog Number	C4033375
EU RoHS Indicator	No
Style	Auto-Ranging Voltage Indicator, ARVI (69kV - 500kV)
UPC	096359368144

Dimensions

Weight	5.5 lb
WeightMetric	2.4 kg

Electrical Ratings

Withstand Voltage	69kV - 500kV
-------------------	--------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	1
Standard Package	1

Product Assets

[Catalogs - Instruments and Meters](#)
[Installation Manuals - CHANCE Auto-Ranging Voltage Indicator \(ARVI\) Operating Instructions](#)
[Specifications - C4033375](#)